

## TECHNICAL DATA

**Capacity under lid** 19lt / 5gal

**Lid** LR1920 - Tear Strip  
Optional Spout and/or Vent  
SLR3 - Snap on Lid

<b>Wall Thickness</b>	Pail PR1900	2.29mm	0.090in
	Lid LR1920	1.93mm	0.076in
	Lid SLR3	1.93mm	0.076in

<b>Weight (approx.) without bail</b>	Pail PR1900	890g	31.39oz
	Lid LR1920	254g	8.96oz
	Lid LRF1920	254g	8.96oz
	Lid LVF1920	254g	8.96oz
	Lid SLR3	173g	6.10oz

**Material** HDPE

**Handle** Plastic or Metal

**Thermal range** -18°C (0°F) to 66°C (150°F)

**Printing** Dry Offset - Up to 6 Colours,  
Heat Transfer Label, In Mold Labelling

**Pail Colour** Standard in White,  
other colors available.

## TOP LOADING RESISTANCE

60kg (132lbs) at 23°C (73°F), 30 days, product temperature when filling pails and warehouse temperature will affect pail performance. Hofmann recommends testing prior to full production.

## OPENING & CLOSING

TO OPEN: Remove tear strip, then lift cover.

TO CLOSE: Place lid on pail, press on with hands or use a rubber mallet.

## RECOMMENDATIONS

Do not exceed pallet edges with pails. Grade A pallets should be used with boards that have tight spacing to ensure proper pail support. To improve stability, release air from pail when applying the lid. Stretch wrapping machine tension should be adjusted to ensure no deformation of the pail. Use slip-sheet to improve pails stability. Hofmann recommends testing prior to full production.

## APPROVALS

Virgin materials are approved for food contact and meet FDA (Food and Drug Administration USA) and HPB (Health Protection Branch Canada) regulations.

Handling conditions vary a lot from customer to customer. Tests are recommended throughout the process of denesting, filling, conveying palletization, warehousing, transportation and utilization by intermediaries and users. Specifications can change without notice. Please contact your Hofmann representative to confirm this data.

## PRODUCT CODE

**PAIL:** PR1900

**LID:** LR1920 or SLR3



## DIMENSIONS

	CM	INCHES
Pail Height	37.2	14.63
Pail Height with Lid	37.5	14.75
Upper width with Lid	31	12.21
Lower Width	26.4	10.38

## PACKAGING OF EMPTY PAILS & LIDS

- Warehousing of empty pails:  
132 per tray - 264 per pallet
- Warehousing of LR1920 Lids:  
300 per tray - 600 per pallet  
SLR3: 1200 per pallet
- Max 2 pallets high for warehousing of pails
- Max 4 pallets high for warehousing of lids

