Product Specifications Tamper Evident

e.HOFMANN

PLASTICS

TECHNICAL DATA			
Capacity under lid	3.80L /1.0 gal		
Wall Thickness	Pail PR380 Lid LR300	0.88mm 0.98mm	0.000
Weight (approx.) without bail	Pail PR380 Lid LR300	100g 40g	3.53oz 1.41oz
Pail Material	Polypropylene		

Pail Material	Polypropylene
Handle	None
Thermal range	-18°C (0°F) to 66°C (150°F)
Printing	Dry Offset - Up to 6 Colours
Pail Colour	Standard in White, other colors available.

TOP LOADING RESISTANCE

45kg (99lb) at 23°C (73°F), 30 days, product temperature when filling pails and warehouse temperature will affect pail performance. Hofmann recommends testing prior to full production.

OPENING & CLOSING

TO OPEN: Lift snap on cover.

TO CLOSE: Place lid on pail, press on with hands.

RECOMMENDATIONS

Do not exceed pallet edges with pails. Grade A pallets should be used with boards that have tight spacing to ensure proper pail support. To improve stability, release air from pail when applying the lid. Stretch wrapping machine tension should be adjusted to ensure no deformation of the pail. Use slip-sheet to improve pails stability. Hofmann recommends testing prior to full production.

APPROVALS

Virgin materials are approved for food contact and meet FDA (Food and Drug Administration USA) and HPB (Health Protection Branch Canada) regulations.

ADVISE

Handling conditions vary a lot from customer to customer. Tests are recommended throughout the process of denesting, filling, conveying palletization, warehousing, transportation and utilization by intermediaries and users. Specifications can change without notice. Please contact your Hofmann representative to confirm this data.

PRODUCT CODE

PAIL: PR380 LID: LR300



DIMENSIONS	CM	INCHE
Pail Height	15.2	6
Pail Height with Lid	15.4	6.2
Upper width with Lid	20.5	8.10
Lower Width	17.8	7.0

PACKAGING OF EMPTY PAILS & LIDS

- Warehousing of empty pails: 120 per box 2.400 per pallet
- Warehousing of LR300 Lids: 240 per box 7200 per pallet

RECOMMENDATIONS

 Max 2 pallets high for warehousing of pails







