Product Specifications Heavy Duty

e. **HOFMANN** PLASTICS

TECHNICAL DATA

| Capacity under lid | 19lt / 5gal | | |
|----------------------------------|--|--|-------------------------------|
| Lid | LRT1922 - Tear Strip Lid LRF1920 - Tear Strip with Flexspout LFV1920 - Tear Strip with Flexspout and Vent SLR3 - Snap on Lid | | |
| Wall Thickness | Pail PR1910 Lid LRT1922 Lid LRF1920 Lid LFV1920 Lid SLR3 | 2.29mm 2.03mm 2.03mm 2.03mm 1.93mm | 0.080in 0.080in 0.080in |
| Weight (approx.) without bail | Pail PR1910 Lid LRT1922 Lid LRF1920 Lid LFV1920 Lid SLR3 | 895g 246g 248g 248g 171g | 8.67oz 8.74oz |
| Material | HDPE | | |
| Handle | Plastic or Metal | | |
| Thermal range | -18°C (0°F) to 66°C (150°F) | | |
| Printing | Dry Offset - Up to 6 Colours, Heat Transfer Label, In Mold Labelling | | |

Pail Colour

Standard in White, other colors available.

TOP LOADING RESISTANCE

60kg (132lbs) at 23°C (73°F), 30 days, product temperature when filling pails and warehouse temperature will affect pail performance. Hofmann recommends testing prior to full production.

OPENING & CLOSING

TO OPEN: Remove tear strip, then lift cover.

TO CLOSE: Place lid on pail, press on with hands or use a rubber mallet.

RECOMMENDATIONS

Do not exceed pallet edges with pails. Grade A pallets should be used with boards that have tight spacing to ensure proper pail support. To improve stability, release air from pail when applying the lid. Stretch wrapping machine tension should be adjusted to ensure no deformation of the pail. Use slip-sheet to improve pails stability. Hofmann recommends testing prior to full production.

APPROVALS

Virgin materials are approved for food contact and meet FDA (Food and Drug Administration USA) and HPB (Health Protection Branch Canada regulations.

Handling conditions vary a lot from customer to customer. Tests are recommended throughout the process of denesting, filling, conveying palletization, warehousing, transportation and utilization by intermediaries and users. Specifications can change without notice. Please contact your Hofmann representative to confirm this data.



PRODUCT CODE


PAIL: PR1910 **LID:** LRT1922, LRF1920, LFV1920, or SLR3



| DIMENSIONS | СМ | INCHES |
|----------------------|-------|--------|
| Pail Height | 37.24 | 14.34 |
| Pail Height with Lid | 37.08 | 14.60 |
| Upper width with Lid | 31.75 | 12.15 |
| Lower Width | 26.03 | 10.25 |

PACKAGING OF EMPTY PAILS & LIDS

- Warehousing of empty pails: 144 per tray - 288 per pallet
- Warehousing of LRT1922/LRF1920/ LFV1920 Lids: 300 per tray - 600 per pallet SLR3: 1200 per pallet ______
- Max 2 pallets high for warehousing of pails
- Max 4 pallets high for warehousing of lids



E. Hofmann Plastics Inc. • 51 Centennial Road, Orangeville, Ontario, Canada L9W 3R1 Telephone: 519-943-5050 • Toll Free: 1-877-707-Pail • Fax: 519-938-5349 • www.hofmannplastics.com