

TECHNICAL DATA

Capacity under lid	20lt / 5.5 gal		
Wall Thickness	Pail PR2000	2.29mm	0.090in
	Lid LR1940	1.93mm	0.076in
	Lid SLR3	1.93mm	0.076in
Weight (aprox.) without bail	Pail PR2000	970g	34.22oz
	Lid LR1940	254g	8.96oz
	Lid LRF1920	254g	8.96oz
	Lid LVF1920	254g	8.96oz
	Lid SLR3	173g	6.10oz
Pail Material	HDPE		
Handle	Plastic or Metal		
Thermal range	-18°C (0°F) to 66°C (150°F)		
Printing	In Mold Labelling, Dry Offset - Up to 6 Colours		
Pail Colour	Standard in White, other colors available.		

TOP LOADING RESISTANCE

60kg (132lb) at 23°C (73°F), 30 days, product temperature when filling pails and warehouse temperature will affect pail performance. Hofmann recommends testing prior to full production.

OPENING & CLOSING

TO OPEN: Remove tear strip, then lift cover.

TO CLOSE: Place lid on pail, press on with hands or use a rubber mallet.

RECOMMENDATIONS

Do not exceed pallet edges with pails. Grade A pallets should be used with boards that have tight spacing to ensure proper pail support.

To improve stability, release air from pail when applying the lid. Stretch wrapping machine tension should be adjusted to ensure no deformation of the pail. Use slip-sheet to improve pails stability. Hofmann recommends testing prior to full production.

APPROVALS

Virgin materials are approved for food contact and meet FDA (Food and Drug Administration USA) and HPB (Health Protection Branch Canada) regulations.

ADVISE

Handling conditions vary a lot from customer to customer. Tests are recommended throughout the process of denesting, filling, conveying palletization, warehousing, transportation and utilization by intermediaries and users. Specifications can change without notice. Please contact your Hofmann representative to confirm this data.

PRODUCT CODE

PAIL: PR2000

LID: LR1940, LRF1920, LRFV1920, OR SLR3



DIMENSIONS

	CM	INCHES
Pail Height	40	15.75
Pail Height with Lid	40.3	15.9
Upper width with Lid	31	12.21
Lower Width	26.3	10.35

PACKAGING OF EMPTY PAILS & LIDS

- Warehousing of empty pails:
204 per pallet
- Warehousing of LR1940 Lids:
300 per tray - 600 per pallet
- SLR3: 1200 per pallet

RECOMMENDATIONS

- Max 2 pallets high for warehousing of pails

