Product Specifications TE350 + TLR235

e.HOFMANN

PLASTICS

TECHNICAL DATA					
Capacity under lid	.34L / 12.0 us oz				
Pail	TE350		Tamper Evident Container with Tear Tab		
Lid	TLR235	Snap on	Snap on Lid		
Wall Thickness	TE350 TLR235	0.51mm 0.46mm	0.020in 0.018in		
Weight (approx.) without bail	TE350 TLR235	15g 6.5g	0.54oz 0.22oz		
Material	TE350 TLR235	Polypropylene Polypropylene			
Thermal range	0°C (32°F) to 90°C (194°F)				
Decoration	In Mould Labelling				
Standard Color	Standard in White, other colors available				

OPENING & CLOSING

TO OPEN: Break the Tamper-Evident tab, then remove lid. TO CLOSE: Start the lid at one side first, then apply around while releasing air on opposite side. Pressing the center of the lid if needed to burp container.

RECOMMENDATIONS

Do not double stack skids upon one another; racking recommended. Grade A pallets should be used with boards that have tight spacing to ensure proper box support. Stretch wrapping machine tension should be adjusted to ensure no deformation of the boxes. Hofmann recommends testing prior to full production.

APPROVALS

Virgin materials are approved for food contact and meet FDA (Food and Drug Administration USA) and HPB (Health Protection Branch Canada) regulations.

HANDLING

Handling conditions vary from customer to customer. Tests are recommended throughout the process of denesting, filling, conveying palletization, warehousing, transportation and utilization by intermediaries and users. Specifications can change without notice. Please contact your Hofmann representative to confirm.

PAIL: TE350 (120Z)

LID: TLR235



DIMENSIONS	СМ	INCHE
Lower Diameter	9.50	3.74
Upper Diameter with Lid	12.01	4.73
Upper Width with Lid	12.01	4.73
Height with Lid	5.97	2.35

PACKAGING OF EMPTY PAILS & LIDS

- Warehousing of empty pails: TE350 740 per box (20 box per pallet) 14,800 per skid TLR235 1,000 per box (48 box per pallet) 48,000 per skid
- Max 2 pallets high for warehousing of Pails
- Max 2 pallets high for warehousing of Lids





