Product Specifications TE500 + TLR235

e. HOFMANN

TECHNICAL DATA					
Capacity under lid	.500L / 16 us oz				
Pail	TE500	Tamper Evident Container with Tear Tab			
Lid	TLR235	Snap on Lid			
Wall Thickness	TE500 TLR235	0.51mm 0.45mm			
Weight (approx.) without bail	TE500 TLR235	18.8g 6.2g	0.66oz 0.22oz		
Material	TE500 TLR235	Polypropylene Polypropylene			
Thermal range	0°C (32°F) to 90°C (194°F)				
Decoration	In Mould Labelling				
Standard Color	Standard in White, other colors available				

OPENING & CLOSING

TO OPEN: Break the Tamper-Evident tab, then remove lid. TO CLOSE: Start the lid at one side first, then apply around while releasing air on opposite side. Pressing the center of the lid if needed to burp container.

RECOMMENDATIONS

Do not double stack skids upon one another; racking recommended. Grade A pallets should be used with boards that have tight spacing to ensure proper box support. Stretch wrapping machine tension should be adjusted to ensure no deformation of the boxes. Hofmann recommends testing prior to full production.

APPROVALS

Virgin materials are approved for food contact and meet FDA (Food and Drug Administration USA) and HPB (Health Protection Branch Canada) regulations.

HANDLING

Handling conditions vary from customer to customer. Tests are recommended throughout the process of denesting, filling, conveying palletization, warehousing, transportation and utilization by intermediaries and users. Specifications can change without notice. Please contact your Hofmann representative to confirm.

PLASTICS PRODUCT CODE

PAIL: TE500 (16 OZ) LID: TLR235		
TE500		
TLR235		

DIMENSIONS	СМ	INCHE
Lower Diameter	9.09	3.58
Upper Diameter with Lid	12.01	4.73
Upper Width with Lid	11.94	4.7
Height with Lid	8.20	3.23

PACKAGING OF EMPTY PAILS & LIDS

- Warehousing of empty pails:
- Max 2 pallets high for





